



### Maxi Vision Hood

## Maxi Vision Hood in HiGlo Buckle Closure

077-6112-\*\*\*\*

Maxi Vision Hood Buckle Closure.

**Requires Valve Belt Assembly sold separately.**

*This hood is shown with 072-4354 Jacket and 074-4046 Bib Overalls sold separately and the Zip Clip for Hard Cap headgear option.*

*Any asterisk (\*) shown in an Item No. will be replaced with a combination of digits identifying all of the options selected.*

The Maxi-Vision Hood offers wide-angle vision furnished by a multi-dimensional hood. This enlarged hood adapts to twin cartridge respirator, an airline respirator and most SCBA's. The inner ring allows for easy attachment to the user's hard hat and keeps it in place. Maxi Vision Hoods with ventilation air capability require the use of the Valve Belt assembly (sold separately) to energize the Hood. The 16" X 11" clear-flex window provides the wearer with a better viewing range than most standard hoods. The rear bib is large enough to cover the upper portion of an air tank. Underarm straps with plastic quick release fittings hold the hood close to the body. The Maxi Vision Hood is manufactured to order.

### Limitation of Liability

This information is based upon technical data that Standard Safety Equipment Company believes to be reliable. It is subject to revision as additional knowledge and experience are gained. Standard Safety Equipment Company makes no guarantee of results and assumes no obligation or liability in connection with this information. It is the user's responsibility to determine the level of toxicity and the proper personal protective equipment needed. The information set forth herein reflects laboratory performance of fabrics not complete garments, under controlled conditions. It is intended for information use by persons having technical skill for evaluation under their specific end-use conditions, at their own discretion and risk. Anyone intending to use this information should first verify that the garment selected is suitable for the intended use. In many cases, seams and closures have shorter breakthrough times and higher permeation rates than the fabric. Please contact the garment manufacturer for specific data. If fabric becomes torn, abraded, or punctured, end user should discontinue use of garment to avoid potential exposure to chemical. Since conditions of use are outside our control, we make no warranties, express or implied, including without limitations, no warranties of merchantability or fitness for a particular use and assume no liability in connection with any use of this information. This information is not intended as a license to operate under or a recommendation to infringe any patent or technical information of Standard Safety Equipment Company or others covering any material or its use.

## Maxi Vision Hood in HiGlo Buckle Closure

077-6112-\*\*\*\*

### Specs

Closure-MV Hood:	Buckle Closure
Fabric:	HiGlo
Headgear-MV Hood:	<b>Available options:</b> <ul style="list-style-type: none"><li>• Zip Clip for Hard Cap</li><li>• Zip Clip with Extenders for a Hard Cap</li><li>• Zip Clip with Included Hard Cap</li><li>• Zip Clip with Extenders and Included Hard Cap</li></ul>
Units:	Each
Window-MV Hood:	40 mil Window - No Cover Window
Additional Garment Options:	<b>Available options:</b> <ul style="list-style-type: none"><li>• Imprinted</li></ul>

### Related Products



#### **Belt and Offset Valve Block with Fitting**

145-1000-\*\*\*\*

Belt with an adjustable valve block installed on the side for easy access by the wearer. Choose one of five fittings to include with the assembly. Photo is shown with Hansen fitting.



#### **Contact Us:**

Toll Free: (888) 345-4773

Phone: (815) 363-8565

[info@standardsafety.com](mailto:info@standardsafety.com)

[www.standardsafety.com](http://www.standardsafety.com)

### Limitation of Liability

This information is based upon technical data that Standard Safety Equipment Company believes to be reliable. It is subject to revision as additional knowledge and experience are gained. Standard Safety Equipment Company makes no guarantee of results and assumes no obligation or liability in connection with this information. It is the user's responsibility to determine the level of toxicity and the proper personal protective equipment needed. The information set forth herein reflects laboratory performance of fabrics not complete garments, under controlled conditions. It is intended for information use by persons having technical skill for evaluation under their specific end-use conditions, at their own discretion and risk. Anyone intending to use this information should first verify that the garment selected is suitable for the intended use. In many cases, seams and closures have shorter breakthrough times and higher permeation rates than the fabric. Please contact the garment manufacturer for specific data. If fabric becomes torn, abraded, or punctured, end user should discontinue use of garment to avoid potential exposure to chemical. Since conditions of use are outside our control, we make no warranties, express or implied, including without limitations, no warranties of merchantability or fitness for a particular use and assume no liability in connection with any use of this information. This information is not intended as a license to operate under or a recommendation to infringe any patent or technical information of Standard Safety Equipment Company or others covering any material or its use.