



#### Shoulder Mount Hood

### Enlarged Shoulder Mount Hood in GraLite® 20 Chest Length Buckle Closure Cover Window

077-6639-\*\*\*\*

#### Enlarged Shoulder Mount Hood

- GraLite® 20 fabric
- Chest length
- Buckle closure
- Standard size window
- Cover window w/o snaps

**Requires Valve Belt Assembly sold separately.**

*Any asterisk (\*) shown in an Item No. will be replaced with a combination of digits identifying all of the options selected.*

StaSafe® Shoulder-Mounted Hood is ideal for long hours of work because there is no restrictive headgear. The weight of the hood rests on the shoulders. Adjustable underarm straps hold the front and rear bibs close to the body for comfort and splash protection. The viewing window is constructed of a 40 mils vinyl and permanently sealed to the hood and is protected by a clear, replaceable 20 mils acetate splash window on the outside. A 3/8" I.D. air supply tube extends to the top of the hood. Available in chest length or waist length. Shoulder Mount Hood designs are manufactured to order.

#### Limitation of Liability

This information is based upon technical data that Standard Safety Equipment Company believes to be reliable. It is subject to revision as additional knowledge and experience are gained. Standard Safety Equipment Company makes no guarantee of results and assumes no obligation or liability in connection with this information. It is the user's responsibility to determine the level of toxicity and the proper personal protective equipment needed. The information set forth herein reflects laboratory performance of fabrics not complete garments, under controlled conditions. It is intended for information use by persons having technical skill for evaluation under their specific end-use conditions, at their own discretion and risk. Anyone intending to use this information should first verify that the garment selected is suitable for the intended use. In many cases, seams and closures have shorter breakthrough times and higher permeation rates than the fabric. Please contact the garment manufacturer for specific data. If fabric becomes torn, abraded, or punctured, end user should discontinue use of garment to avoid potential exposure to chemical. Since conditions of use are outside our control, we make no warranties, express or implied, including without limitations, no warranties of merchantability or fitness for a particular use and assume no liability in connection with any use of this information. This information is not intended as a license to operate under or a recommendation to infringe any patent or technical information of Standard Safety Equipment Company or others covering any material or its use.

## Enlarged Shoulder Mount Hood in GraLite® 20 Chest Length Buckle Closure Cover Window

077-6639-\*\*\*\*

### Specs

Hood-SM Hood:	Enlarged Shoulder Mount Hood
Fabric:	GraLite® 20
Length-SM Hood:	Chest Length
Units:	Each
Closure-SM Hood:	Buckle Closure for Chest Length Hoods
Window Style:	Standard size window - cover window frame flaps - cover window installs in flaps
Window/Cover Window Options -SM Hood:	<b>Available options:</b> <ul style="list-style-type: none"><li>• 20 mil Cover Window</li><li>• 40 mil Cover Window</li></ul>
Window - Cover Window Replacement Packs - SM Hood [ss]:	<b>Available options:</b> <ul style="list-style-type: none"><li>• 077-1012-5424 - 20 mil Std Size Cover Window (option for standard size window with bottom flap)</li><li>• 077-1012-5760 - 40 mil Std Size Cover Window (option for standard size window with bottom flap)</li><li>• 077-1012-6512 - 20 mil Std Size Cover Window (option for standard size window without bottom flap)</li><li>• 077-1012-6828 - 20 mil Cover Window (option for over-sized window)</li><li>• 077-1012-6829 - 40 mil Cover Window (option for over-sized window)</li></ul>
Long Air Line:	YES
Additional Garment Options:	<b>Available options:</b> <ul style="list-style-type: none"><li>• Imprinted</li></ul>

### Related Products



#### Belt and Offset Valve Block with Fitting

145-1000-\*\*\*\*

Belt with an adjustable valve block installed on the side for easy access by the wearer. Choose one of five fittings to include with the assembly. Photo is shown with Hansen fitting.

### Limitation of Liability

This information is based upon technical data that Standard Safety Equipment Company believes to be reliable. It is subject to revision as additional knowledge and experience are gained. Standard Safety Equipment Company makes no guarantee of results and assumes no obligation or liability in connection with this information. It is the user's responsibility to determine the level of toxicity and the proper personal protective equipment needed. The information set forth herein reflects laboratory performance of fabrics not complete garments, under controlled conditions. It is intended for information use by persons having technical skill for evaluation under their specific end-use conditions, at their own discretion and risk. Anyone intending to use this information should first verify that the garment selected is suitable for the intended use. In many cases, seams and closures have shorter breakthrough times and higher permeation rates than the fabric. Please contact the garment manufacturer for specific data. If fabric becomes torn, abraded, or punctured, end user should discontinue use of garment to avoid potential exposure to chemical. Since conditions of use are outside our control, we make no warranties, express or implied, including without limitations, no warranties of merchantability or fitness for a particular use and assume no liability in connection with any use of this information. This information is not intended as a license to operate under or a recommendation to infringe any patent or technical information of Standard Safety Equipment Company or others covering any material or its use.



**Contact Us:**

Toll Free: (888) 345-4773

Phone: (815) 363-8565

[info@standardsafety.com](mailto:info@standardsafety.com)

[www.standardsafety.com](http://www.standardsafety.com)

---

### **Limitation of Liability**

This information is based upon technical data that Standard Safety Equipment Company believes to be reliable. It is subject to revision as additional knowledge and experience are gained. Standard Safety Equipment Company makes no guarantee of results and assumes no obligation or liability in connection with this information. It is the user's responsibility to determine the level of toxicity and the proper personal protective equipment needed. The information set forth herein reflects laboratory performance of fabrics not complete garments, under controlled conditions. It is intended for information use by persons having technical skill for evaluation under their specific end-use conditions, at their own discretion and risk. Anyone intending to use this information should first verify that the garment selected is suitable for the intended use. In many cases, seams and closures have shorter breakthrough times and higher permeation rates than the fabric. Please contact the garment manufacturer for specific data. If fabric becomes torn, abraded, or punctured, end user should discontinue use of garment to avoid potential exposure to chemical. Since conditions of use are outside our control, we make no warranties, express or implied, including without limitations, no warranties of merchantability or fitness for a particular use and assume no liability in connection with any use of this information. This information is not intended as a license to operate under or a recommendation to infringe any patent or technical information of Standard Safety Equipment Company or others covering any material or its use.