

Shoulder Mount Hood

Shoulder Mount Hood in WinterGlo 20 Waist Length Hook & Loop Closure Over-sized Window Cover Window

077-6980-****



Shoulder Mount Hood

- WinterGlo 20 fabric
- Waist length
- Hook & loop closure
- Over-sized window
- Cover window w/snaps

Requires Valve Belt Assembly

Valve Belt with fitting is an available option - See below

The 072-5522 Jacket and 074-5516 Bib Overalls are sold separately.

Any asterisk () shown in an Item No. will be replaced with a combination of digits identifying all of the options selected.*

StaSafe® Shoulder-Mounted Hood is ideal for long hours of work because there is no restrictive headgear. The weight of the hood rests on the shoulders. Adjustable underarm straps hold the front and rear bibs close to the body for comfort and splash protection. The viewing window is constructed of a 40 mils vinyl and permanently sealed to the hood and is protected by a clear, replaceable 20 mils acetate splash window on the outside. A 3/8" I.D. air supply tube extends to the top of the hood. Available in chest length or waist length. Shoulder Mount Hood designs are manufactured to order.

Limitation of Liability

This information is based upon technical data that Standard Safety Equipment Company believes to be reliable. It is subject to revision as additional knowledge and experience are gained. Standard Safety Equipment Company makes no guarantee of results and assumes no obligation or liability in connection with this information. It is the user's responsibility to determine the level of toxicity and the proper personal protective equipment needed. The information set forth herein reflects laboratory performance of fabrics not complete garments, under controlled conditions. It is intended for information use by persons having technical skill for evaluation under their specific end-use conditions, at their own discretion and risk. Anyone intending to use this information should first verify that the garment selected is suitable for the intended use. In many cases, seams and closures have shorter breakthrough times and higher permeation rates than the fabric. Please contact the garment manufacturer for specific data. If fabric becomes torn, abraded, or punctured, end user should discontinue use of garment to avoid potential exposure to chemical. Since conditions of use are outside our control, we make no warranties, express or implied, including without limitations, no warranties of merchantability or fitness for a particular use and assume no liability in connection with any use of this information. This information is not intended as a license to operate under or a recommendation to infringe any patent or technical information of Standard Safety Equipment Company or others covering any material or its use.

Shoulder Mount Hood in WinterGlo 20 Waist Length Hook & Loop Closure Over-sized Window Cover Window

077-6980-****

Specs

Hood-SM Hood:	Shoulder Mount Hood
Fabric:	WinterGlo 20
Length-SM Hood:	Waist Length
Units:	Each
Closure-SM Hood:	Hook & Loop Closure for Waist Length Hoods
Window Style:	Over-sized window - no bottom flap - cover window has snaps
Window/Cover Window Options -SM Hood:	Available options: <ul style="list-style-type: none">• 20 mil Cover Window• 40 mil Cover Window
Window - Cover Window Replacement Packs - SM Hood [ss]:	Available options: <ul style="list-style-type: none">• 077-1012-5424 - 20 mil Std Size Cover Window (option for standard size window with bottom flap)• 077-1012-5760 - 40 mil Std Size Cover Window (option for standard size window with bottom flap)• 077-1012-6512 - 20 mil Std Size Cover Window (option for standard size window without bottom flap)• 077-1012-6828 - 20 mil Cover Window (option for over-sized window)• 077-1012-6829 - 40 mil Cover Window (option for over-sized window)
Optional Valve Belt [AO]:	Available options: <ul style="list-style-type: none">• Valve Belt with Hansen Fitting• Valve Belt with Schrader Fitting• Valve Belt with Snap-Tite® Fitting• Valve Belt with Brass Snap-Tite® Fitting• Valve Belt with Tru-Flate® Fitting
Additional Garment Options:	Available options: <ul style="list-style-type: none">• Imprinted

Related Products

Limitation of Liability

This information is based upon technical data that Standard Safety Equipment Company believes to be reliable. It is subject to revision as additional knowledge and experience are gained. Standard Safety Equipment Company makes no guarantee of results and assumes no obligation or liability in connection with this information. It is the user's responsibility to determine the level of toxicity and the proper personal protective equipment needed. The information set forth herein reflects laboratory performance of fabrics not complete garments, under controlled conditions. It is intended for information use by persons having technical skill for evaluation under their specific end-use conditions, at their own discretion and risk. Anyone intending to use this information should first verify that the garment selected is suitable for the intended use. In many cases, seams and closures have shorter breakthrough times and higher permeation rates than the fabric. Please contact the garment manufacturer for specific data. If fabric becomes torn, abraded, or punctured, end user should discontinue use of garment to avoid potential exposure to chemical. Since conditions of use are outside our control, we make no warranties, express or implied, including without limitations, no warranties of merchantability or fitness for a particular use and assume no liability in connection with any use of this information. This information is not intended as a license to operate under or a recommendation to infringe any patent or technical information of Standard Safety Equipment Company or others covering any material or its use.



Belt and Offset Valve Block with Fitting

145-1000-****

Belt with an adjustable valve block installed on the side for easy access by the wearer. Choose one of five fittings to include with the assembly. Photo is shown with Hansen fitting.



Contact Us:

Toll Free: (888) 345-4773

Phone: (815) 363-8565

info@standardsafety.com

www.standardsafety.com

Limitation of Liability

This information is based upon technical data that Standard Safety Equipment Company believes to be reliable. It is subject to revision as additional knowledge and experience are gained. Standard Safety Equipment Company makes no guarantee of results and assumes no obligation or liability in connection with this information. It is the user's responsibility to determine the level of toxicity and the proper personal protective equipment needed. The information set forth herein reflects laboratory performance of fabrics not complete garments, under controlled conditions. It is intended for information use by persons having technical skill for evaluation under their specific end-use conditions, at their own discretion and risk. Anyone intending to use this information should first verify that the garment selected is suitable for the intended use. In many cases, seams and closures have shorter breakthrough times and higher permeation rates than the fabric. Please contact the garment manufacturer for specific data. If fabric becomes torn, abraded, or punctured, end user should discontinue use of garment to avoid potential exposure to chemical. Since conditions of use are outside our control, we make no warranties, express or implied, including without limitations, no warranties of merchantability or fitness for a particular use and assume no liability in connection with any use of this information. This information is not intended as a license to operate under or a recommendation to infringe any patent or technical information of Standard Safety Equipment Company or others covering any material or its use.