

TEG

Rear Entry TEG in CPE Attached CPE Stocking Foot Booties SCBA Pouch Egress Pouch AC and Special Reinforcements

076-7050-****

This suit is an illustration of our customization capabilities. It has a rear entry and CPE stocking foot booties.

Special attributes included in this design are:

- Pouch for an egress bottle on hip
- Pouch for SCBA on back
- Pass-through reinforcement
- Comm pass-through reinforcement
- 4" x 12.5" AC reinforcement
- Includes an Encon 17CFM AC Unit With Strainer Tee and Schrader 1/2" Fitting.

This configuration shows the addition of a Brass Pass-through and a communication pass-through sold separately.

Any asterisk () shown in an Item No. will be replaced with a combination of digits identifying all of the options selected.*



The AcidMaster®, ChemMaster® and WorkMaster® configurations have been designed from input by the end user to accommodate their specific needs. If you do not see the exact design required to fit your application Standard Safety will help you custom design a garment for your specific application. Once considered a custom design and now a standard, we had many requests to combine in one suit a SCBA and an egress bottle pouch to allow dual purpose use. It is now part of our standard offering. TEG designs are manufactured to order. Video demonstrations on the installation and removal of the SealTite® Sleeve Insert and Gloves are available in the SUPPORT link on our website.

Limitation of Liability

This information is based upon technical data that Standard Safety Equipment Company believes to be reliable. It is subject to revision as additional knowledge and experience are gained. Standard Safety Equipment Company makes no guarantee of results and assumes no obligation or liability in connection with this information. It is the user's responsibility to determine the level of toxicity and the proper personal protective equipment needed. The information set forth herein reflects laboratory performance of fabrics not complete garments, under controlled conditions. It is intended for information use by persons having technical skill for evaluation under their specific end-use conditions, at their own discretion and risk. Anyone intending to use this information should first verify that the garment selected is suitable for the intended use. In many cases, seams and closures have shorter breakthrough times and higher permeation rates than the fabric. Please contact the garment manufacturer for specific data. If fabric becomes torn, abraded, or punctured, end user should discontinue use of garment to avoid potential exposure to chemical. Since conditions of use are outside our control, we make no warranties, express or implied, including without limitations, no warranties of merchantability or fitness for a particular use and assume no liability in connection with any use of this information. This information is not intended as a license to operate under or a recommendation to infringe any patent or technical information of Standard Safety Equipment Company or others covering any material or its use.

Rear Entry TEG in CPE Attached CPE Stocking Foot Booties SCBA Pouch Egress Pouch AC and Special Reinforcements

076-7050-****

Specs

Type-TEG:	TEG
Fabric:	CPE
Entry-TEG:	Rear Entry
Units:	Each
Sizes:	All Sizes
Gloves for CPE Fabric:	Available options: <ul style="list-style-type: none">• Black Butyl• Black Neoprene• Heavy Duty Black Neoprene• View Gloves & Sleeves category for specialty glove availability
Attached Footwear-TEG:	Attached CPE Stocking Foot Booties
Boots Available with Stocking Foot Booties-TEG:	Available options: <ul style="list-style-type: none">• PVC Composite-safety-toe Boots
AC-Vent-TEG:	AC Unit
Pass-through Available [ss]:	YES
Customer-supplied Pass-through Installation Available [ss]:	YES
Pouch-TEG:	Double Pouch
Additional Garment Options:	Available options: <ul style="list-style-type: none">• Imprinted• Addition of 1 or 2 pockets available• +/- 3" increments to sleeve length available• Addition of hang-up loops
Retrieval D-Ring Available [ss]:	YES

Related Products

Limitation of Liability

This information is based upon technical data that Standard Safety Equipment Company believes to be reliable. It is subject to revision as additional knowledge and experience are gained. Standard Safety Equipment Company makes no guarantee of results and assumes no obligation or liability in connection with this information. It is the user's responsibility to determine the level of toxicity and the proper personal protective equipment needed. The information set forth herein reflects laboratory performance of fabrics not complete garments, under controlled conditions. It is intended for information use by persons having technical skill for evaluation under their specific end-use conditions, at their own discretion and risk. Anyone intending to use this information should first verify that the garment selected is suitable for the intended use. In many cases, seams and closures have shorter breakthrough times and higher permeation rates than the fabric. Please contact the garment manufacturer for specific data. If fabric becomes torn, abraded, or punctured, end user should discontinue use of garment to avoid potential exposure to chemical. Since conditions of use are outside our control, we make no warranties, express or implied, including without limitations, no warranties of merchantability or fitness for a particular use and assume no liability in connection with any use of this information. This information is not intended as a license to operate under or a recommendation to infringe any patent or technical information of Standard Safety Equipment Company or others covering any material or its use.



Inflation Test Kit

149-1126-0000

The StaSafe® Inflation Test Kit accurately measures the air tightness of a Total Encapsulating Garment (TEG). The TEG should be tested after each use and at least once every six months to ensure i...



Stoppers for use with the Inflation Test Kit

149-1126-0100

Pack of 4 replacement stoppers for the Inflation Test Kit.



Contact Us:

Toll Free: (888) 345-4773

Phone: (815) 363-8565

info@standardsafety.com

www.standardsafety.com

Limitation of Liability

This information is based upon technical data that Standard Safety Equipment Company believes to be reliable. It is subject to revision as additional knowledge and experience are gained. Standard Safety Equipment Company makes no guarantee of results and assumes no obligation or liability in connection with this information. It is the user's responsibility to determine the level of toxicity and the proper personal protective equipment needed. The information set forth herein reflects laboratory performance of fabrics not complete garments, under controlled conditions. It is intended for information use by persons having technical skill for evaluation under their specific end-use conditions, at their own discretion and risk. Anyone intending to use this information should first verify that the garment selected is suitable for the intended use. In many cases, seams and closures have shorter breakthrough times and higher permeation rates than the fabric. Please contact the garment manufacturer for specific data. If fabric becomes torn, abraded, or punctured, end user should discontinue use of garment to avoid potential exposure to chemical. Since conditions of use are outside our control, we make no warranties, express or implied, including without limitations, no warranties of merchantability or fitness for a particular use and assume no liability in connection with any use of this information. This information is not intended as a license to operate under or a recommendation to infringe any patent or technical information of Standard Safety Equipment Company or others covering any material or its use.